# **JUNO**°

Location:

Contact/Phone:

# TRAC-MASTER®

Project:
Fixture Type:

Fixture Accessories

# LIGHT CONTROL ACCESSORIES

### PRODUCT DESCRIPTION

A wide variety of functional accessories are compatible with most Juno trac fixtures.

# **Accessories for Line Voltage PAR/BR Trac Fixtures**

# **Barn Doors**

Adjustable doors control glare. Clamp to spotlight.



#### T71R

Black Barn Doors. For trac fixtures T303, T313, T326, T393, T423. Accepts 3 3/4" diameter color filters and louver.

#### T72BL

Black Bam Doors. For trac fixtures T305, T315, T327, T338, T340, T395, T425. Accepts 4 11/16" diameter color filters and larger

#### T73B

Black Barn Doors. For trac fixtures T307, T317, T328, T342, T397, T427. Accepts 5 1/2" diameter color filters and louver.

#### **T73WH**

White Barn Doors. For trac fixtures T307, T317, T328, T342, T397, T427. Accepts  $5\frac{1}{2}$ " diameter color filters and louver.

#### T74RI

Black Barn Doors. For Flex12 TFG116, TFP116 and Trac12 TL109, TL116, TLP116, Strap trac fixtures T611, T621, TP621, Wishbone T480, Delta 200 T216, TP216 and Mini Spots T430, T431 and T442.

# TW71BL

Black Barn Doors. For Wireform® trac fixtures T435. Accepts T560 series color filters and louver.

### TW72BL

Black Barn Doors. For Wireform® trac fixtures T437. Accepts T570 series color filters and louver.

### TW75B

Black Barn Doors. For Wireform® trac fixtures T433. Accepts T560 series color filters and louver.

# **Accessory Holder**

Clamp to spotlight.



### T560BL

For trac fixtures T303, T313, T326, T393, T423. Accepts 3 3/4" diameter color filters and louver.

### T570BL

For trac fixtures T305, T315, T327, T338, T340, T395, T425. Accepts 4 11/16" diameter color filters and louver.

### T580BI

For trac fixtures T307, T317, T328, T342, T397, T427. Accepts  $5^{-1}/2''$  diameter color filters and louver.

### T660BI

For Strap trac fixtures T613, TP613, Delta 200 T218. Accepts 3 3/4" diameter color filters and louver.

# T670BL

For Strap trac fixtures T614, TP614, TP624, Delta 200 T219. Accepts 4 11/16" diameter color filters and louver.

Product specifications subject to change without notice.

### Louvers

Shields lamp and reduces glare.



#### F5928RI

2 3/4" diameter. With hexagonal cells.

# T569BL

 $3\sqrt[3]{4}$  diameter. With 1/2 square cells.

#### T579BL

 $4^{11}/16''$  diameter. With 1/2'' square cells.

### T589BL

 $5^{1/2}$ " diameter. With 1/2" square cells.

# **Color Filters**



	$2^{3}/4''$	3 3/4"	4 11/16"	5 1/2"	
	Diameter	Diameter	Diameter	Diameter	Description
	T591	T561	T571	T581	Med. Pink
	T592	T562	T572	T582	Warm Red
	T593	T563	T573	T583	Daylight Blue
	T594	T564	T574	T584	Med. Blue
•	T595	T565	T575	T585	Med. Amber
	T596	T566	T576	T586	Med. Green

# **Dichroic Color Correction Filters**

2 3/4"	3 3/4"	4 11/16"	
Diameter	Diameter	Diameter	Description
-	T5618	T5718	Cosmetic Peach Color Correction Filter (2700K) for Halogen
			Lamps
T5919	T5619	T5719	Color Correction Filter (2700K) and UV Filter for Ceramic Metal
			Halide (CMH) Lamps

## **Beam Control Lenses**

**Prismatic Spread Lens** Even pattern prismatic spread lens diffuses beam creating an even overall pattern.

**Linear Spread Lens** Oval pattern linear spread lens directs beam into an elongated oval

Uniformity Lens Eliminates striations without altering size of beam.

**UV Filter** Optivex<sup>TM</sup> Museum Quality UV Filter. Filters out transmission below 400nm.





$2^{3}/4''$	3 3/4"	4 11/16"	
Diameter	Diameter	Diameter	Description
T597	T5677	T5777	Prismatic Spread Lens
T598	T5678	T5778	Linear Spread Lens
T5921	T5621	T5721	Uniformity Lens
T5922	T5622	T5722	UV Filter

# **Eyebrow**

Attachment shields lamp and reduces glare.



# T556BL

For Strap trac fixtures T611, T621, TP621. For Wishbone T480.

### T577BL

For Strap trac fixtures T613, TP613. For Delta 200 T218.

### 587BL

For Strap trac fixtures T614, TP614, T624. For Delta 200 T219. For Wishbone T487



# TRAC-MASTER®

Fixture Accessories

# LIGHT CONTROL ACCESSORIES

# Accessories for Low Voltage Spotlights

# **Barn Doors**

Adjustable doors control glare. Clamp to spotlight.



### T74BL

Black Barn Doors. For Flex12 TFG116, TFP116 and Trac12 TL109, TL116, TLP116, Strap trac fixtures T611, T621, TP621, Wishbone T480, Delta 200 T216, TP216 and  $2^{1/2}$ " diameter Mini Spots T430, T431 and T442.

Black Barn Doors. For use with Flex12 TF130, Trac12 TL117, TL130, TL301, Universal T401 and Trapezia T630 that use MR16 lamps with cover glass. Also requires T7400 Accessory Holder (order separately).

# **Dichroic Color Filters**

To use dichroic color filters, replace clear glass supplied with low voltage lampholders.



1 3/4"	
Diameter	Description
T5501	Red
T5503	Medium Green
T5504	Medium Blue
T5505	Yellow
T5506	Magenta
T5511	Blue-Green (Cyan)
2″	
2" Diameter	Description
-	Description Red
Diameter	
Diameter <b>T7401</b>	Red
Diameter T7401 T7403	Red Medium Green
Diameter T7401 T7403 T7404	Red Medium Green Medium Blue

### Louvers

Shields lamp and reduces glare. Replace clear glass supplied with spotlight.



# T5558BL

1 3/8" diameter. With hexagonal cells.

#### T5559BL

1 3/4" diameter. With hexagonal cells.

#### T7459BL

2" diameter. With hexagonal cells.

# **Dichroic Color Correction Filters**

1 3/4"	2″	
Diameter	Diameter	Description
T5516	T7416	Cool Blue Color Correction Filter (Daylight, 4250K)
T5518	T7418	Cosmetic Peach Color Correction Filter (2700K)
_	T7419	Color Correction Filter (2700K) for Ceramic Metal Halide (CMH) Lamps

# **Color Filters**

To use color filters, replace clear glass supplied with low voltage lampholders.



1 3/4"	
Diameter	Description
T551	Med. Pink
T553	Med. Blue
T555	Med. Amber
2"	
D	B 1.1
Diameter	Description
<u>Diameter</u> <b>T741</b>	Description Med. Pink
T741	Med. Pink
T741 T742	Med. Pink Warm Red
T741 T742 T743	Med. Pink Warm Red Daylight Blue
T741 T742 T743 T744	Med. Pink Warm Red Daylight Blue Med. Blue

### Snoot



### T558BL

From the state of 1 3/4" diameter.

# **Accessory Holder**

Attaches to MR16 lamp without the use of tools or clips.



# T7400BL, SA

For use with Flex12 TF130, TF301, Trac12 TL117, TL130, TL301, Flyback T227, TP216, Universal T401 and Trapezia T630. Accepts up to two 2" media and/or T7470 Barn Doors.

# **Beam Control Lenses**

To use beam control lenses, replace clear glass supplied with low voltage lampholders.

**Diffusion Lens** Creates an even soft pattern.

**Prismatic Spread Lens** Even pattern prismatic spread lens diffuses beam creating an even overall pattern.

Linear Spread Lens Oval pattern linear spread lens directs beam into an elongated oval

**Uniformity Lens** Eliminates striations without altering size of beam.

**UV Filter** Optivex™ Museum Quality UV Filter. Filters out transmission below 400nm.





1 3/4"	2"	
Diameter	Diameter	Description
T557	T7477	Prismatic Spread Lens
T559	T7478	Linear Spread Lens
T5520	T7420	Diffusion Lens
T5521	T7421	Uniformity Lens
T5522	T7422	UV Filter

Product specifications subject to change without notice.

